

HUBBELL
Wiring Device-Kellems

**Straight Blade Devices, Female
Connector Body, Corrosion
Resistant, Industrial/Commercial
Grade, Straight, 2-Pole 3-Wire
Grounding, 20A 125V, 5-20R**

By Hubbell Wiring Device-Kellems
Catalog # [HBL53CM69C](#)

Straight Blade Devices, Female Connector Body, Corrosion
Resistant, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire
Grounding , 20A 125V, 5-20R, Yellow, Single Pack.



General

Application	Industrial/Commercial
Catalog Number	HBL53CM69C
Color	Yellow
Cord Range	0.230"-0.360" (5.8-18.3)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Insulation	Insulated Body
Item Type	Insulgrip Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current Electrical - Dielectric Voltage - Withstands 2,000V minimum Environmental - Flammability - UL 94 HB or better Environmental - IP Suitability - IP20 Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact) Mechanical - Terminal Accommodation - #18-10 AWG. Standed copper wire only Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
Series	Insulgrip
Style	Corrosion Resistant
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Connector Body
UPC	783585161808

Dimensions

Dimensions	2.78 in x 1.52 in x 2.78 in
Display Size	Standard
Height	2.78 in
Length	2.78 in
Weight	0.25 lb
Width	1.52 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#14 AWG to #12 AWG
Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	CSA Certified to C22.2 No. 42 File 280 NEMA® WD-6 Compliant UL Listed to UL498 File E1706
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL53CM69C-SPEC-EN | REV 6/2024