

**Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 20A 250V, 6-20P and White**



By Hubbell Wiring Device-Kellems  
Catalog # [HBL5466CA](#)

Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 20A 250V, 6-20P, Black and White, Single Pack.

**Performance**

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB or better
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Cord Accomodation - .325"-.655"(8.3-16.6)
- Mechanical - Terminal Accommodation - #18-10 AWG. Standed copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

**General**

Catalog Number	HBL5466CA
Color	Black, White
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	2
Item Type	Insulgrip Plug
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Insulgrip®
Specifications	<ul style="list-style-type: none"> <li>• Assembly Screws - Nickel plated steel</li> <li>• Blade Holder - Nylon</li> <li>• Blades - .060 in. (1.5) Brass</li> <li>• Housing/Cord Clamp - Nylon</li> <li>• Terminal Clamp - Nickel plated steel</li> <li>• Terminal Retainer - Clear Polycarbonate</li> <li>• Terminal Screws - #8-32 Brass , multiple drive</li> </ul>
Style	Angled
Type	Plug

UPC 783585174754

**Dimensions**

Dimensions	2.11 in x 1.53 in x 1.22 in
Height	1.22 in
Length	2.11 in
Weight	0.15 lb
Width	1.53 in

**Electrical Ratings**

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	5000 W

**Conductor Related**

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

**Certifications And Compliance**

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified to C22.2 No. 42 File 280</li> <li>• NEMA® WD-6 Compliant</li> <li>• UL Listed to UL498 File E1706</li> </ul>
Nema Rating	6-20P
Standards - RoHS Compliance Status	CM

**Logistics**

Carton Quantity	10
Pallet Quantity	5000

**Product Assets**



**A Hubbell brand**