

Straight Blade Devices, Receptacles, Single, Specification Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Ivory, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5661I](#)



Straight Blade Devices, Receptacles, Single, Specification Grade,
2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Ivory, Single Pack

Application

- Extra Heavy Duty

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - Top: UL 94V-2, Base: UL 94V-0
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL5661I
Color	Ivory
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1.5
Item Type	Single
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> • Auto Self-grounding Clip - Stainless steel • Base - PBT • Face - Nylon • Ground Contact - Brass • Mounting Screws - Zinc plated steel • Mounting Strap - .050" (1.3) Brass

UPC

• Power Contacts - .037 in.
(.9) Brass
783585014005

Dimensions

Dimensions	1.94 in x 1.63 in x 1.19 in
Display Size	Standard Sized Product
Height	1.19 in
Length	1.94 in
Weight	0.15 lb
Width	1.63 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	3750 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA 22.2, No. 42 File 285 • Guide RTRT Fed Spec WC596G • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
Nema Rating	6-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity 10
Pallet Quantity 3600

[Catalogs - WDK Catalog Full 2024](#)
[Literature - EdgeConnect™ Technology FAQ](#)
[Specifications - HBL5661I](#)
[Warranty - Industrial & Commercial Products](#)

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL5661I-SPEC-EN | REV 10/2024