

Straight Blade Devices, Receptacles, Duplex, Specification Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Brown, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5662](#)

Straight Blade Devices, Receptacles, Duplex, Specification
Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Brown, Single
Pack

Application

- Extra Heavy Duty

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - Top: UL 94V-2, Base: UL 94V-0
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL5662
Color	Brown
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1.5
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Automatic Self-grounding Clip - Stainless steel• Base - PBT• Clamping Plate - Nickel plated brass• Face - Nylon



UPC

Dimensions

Dimensions	3.28 in x 1.65 in x 1.19 in
Display Size	Standard Sized Product
Height	1.19 in
Length	3.28 in
Weight	0.25 lb
Width	1.65 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	3750 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

- Mounting Screws - Zinc plated steel
 - Mounting Strap - .050 in. (1.3) Brass
 - Power Contacts - .036 in. (.9) Brass
 - Terminal Screws - Plated brass
 - Wire Clamps - .031 in. (.8) Brass
- 783585435541

Industry Standard(s)

- Certified to CSA 22.2, No. 42 File 285
- Guide RTRT Fed Spec WC596G
- NEMA® WD-6 Compliant
- UL Listed to UL498 File No. E2186

Nema Rating

6-15R

Standards - RoHS Compliance

CM

Status

Logistics

Carton Quantity

10

Pallet Quantity

4500

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - HBL5662](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL5662-SPEC-EN | REV 10/2024