

# Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 15A 277V AC, 7-15P, Black, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5929](#)



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 15A 277V AC, 7-15P, Black, Single Pack.

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB or better
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Cord Accomodation - .310"-.430"(7.9-11.9)
- Mechanical - Terminal Accommodation - #18-12 AWG. Standed copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

## General

Catalog Number	HBL5929
Color	Black
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	2
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Insulprene
Specifications	<ul style="list-style-type: none"><li>• Assembly Screws - Nickel plated steel</li><li>• Blade Holder - Nylon</li><li>• Blades - .060 in. (1.5) Brass</li><li>• Cord Clamp - Plated Steel</li><li>• Housing - Insulprene</li><li>• Terminal Clamp - Nickel plated steel</li><li>• Terminal Screws - #8-32 Brass , multiple drive</li></ul>
Style	Finger Grip
Type	Plug
UPC	783585013251

## Dimensions

Dimensions	1.63 in x 1.5 in x 1.5 in
Height	1.5 in
Length	1.63 in
Weight	0.15 lb
Width	1.5 in

## Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	277 VAC
Voltage Rating Description	277 V
Wattage	4155 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

## Certifications And Compliance

Industry Standard(s)	CSA Certified to C22.2 No. 42 File 280
Nema Rating	7-15P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	4050

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL5929](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL5929-SPEC-EN | REV 10/2024