

Straight Blade Devices, Male Plug, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Yellow, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5965VY](#)

Straight Blade Devices, Male Plug, Valise Series,
Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding,
15A 125V, 5-15P, Yellow, Single Pack.

Application

- Industrial/Commercial Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB or better
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18-12 AWG. Standed copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL5965VY
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	2
Item Type	Valise
Material	Polycarbonate
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Valise®
Specifications	<ul style="list-style-type: none">Assembly Screws - Plated SteelAssembly Screws - Plated steelBlades - BrassCable Inserts - PPOHousing - NylonTerminal Clamp - Nickel plated steelTerminal Screws - #8-32 Brass , multiple drive



Style	Standard
Type	Plug
UPC	783585013091

Dimensions

Dimensions	1.88 in x 1.88 in x 2.55 in
Height	2.55 in
Length	1.88 in
Weight	0.1 lb
Width	1.88 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">CSA Certified to C22.2 No 42 File 280CNEMA® WD-6 CompliantUL Listed to UL498 File E1706
Nema Rating	5-15P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Pallet Quantity

3600

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - HBL5965VY](#)

[Warranty - Industrial & Commercial Products](#)

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL5965VY-SPEC-EN | REV 10/2024