

Straight Blade Devices, Outlet, Flanged, Marine, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Gray, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL61CM65](#)



Straight Blade Devices, Outlet, Flanged, Marine, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Gray, Single Pack.

Application

- Heavy Duty

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL61CM65
Color	Yellow
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Flanged Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Heavy Duty Specification Grade
Specifications	<ul style="list-style-type: none"> • Face - Nylon • Mounting Screw - Stainless steel • Power Contacts - .040" (1.0) Brass • Terminal Screws - #8-32 Brass, Multiple Drive
Style	Weather Proof and Corrosion Resistant

Type	Flanged Receptacle
UPC	783585808673

Dimensions

Dimensions	2.68 in x 2.25 in x 2.68 in
Display Size	Standard Sized Product
Height	2.68 in
Length	2.68 in
Weight	0.25 lb
Width	2.25 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired Only
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 • NEMA® WD-6 Compliant • UL Listed, File E2186
Nema Rating	5-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	550



A Hubbell brand