

Locking Devices, Twist-Lock®, Marine Grade, Female Connector Body, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Galvanized

By Hubbell Wiring Device-Kellems
Catalog # [HBL63CM64](#)



Locking Devices, Twist-Lock®, Marine Grade, Female Connector Body, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Galvanized

General

Application	Marine Wiring Devices
Catalog Number	HBL63CM64
Color	Metallic
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Metallic Body
Item Type	Standard
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Performance	Environmental - Moisture Resistance - IP20 Suitability
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
UPC	783585808727

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	50 A
Current Rating	50 A
Voltage Rating	125/250 VAC

Conductor Related

Conductor Range	#6 AWG
Number of Conductors	4-Wire Grounding

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	Non-NEMA
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5
Pallet Quantity	600

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL63CM64-SPEC-EN | REV 6/2024