

Locking Devices, Twist-Lock®,  
Marine Grade, Male Plug, 50A  
125/250V, 3-Pole 4-Wire  
Grounding, Non-NEMA, Screw  
Terminal, Galvanized

By Hubbell Wiring Device-Kellems  
Catalog # [HBL63CM65](#)



Locking Devices, Twist-Lock®, Marine Grade, Male Plug, 50A  
125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal,  
Galvanized

Application

- Marine Wiring Devices

Performance

Environmental - Moisture Resistance - IP20 Suitability

General

Catalog Number	HBL63CM65
Color	Metallic
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Standard
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Specifications	<ul style="list-style-type: none"><li>Blade Type - Locking</li><li>Housing Type - Standard</li><li>Product Type - Replacement Plugs</li></ul>
UPC	783585808734

Dimensions

Display Size	Standard Sized
--------------	----------------

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	50 A
Current Rating	50 A
Phase	Single Phase
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC
Wattage	12500

Conductor Related

Cord Type	All Listed Portables
Number Of Wires	4-Wire Grounding
Wire Size	#6 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	Non-NEMA

Logistics

Carton Quantity	5
Pallet Quantity	600

Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL63CM65](#)  
[Warranty - Industrial & Commercial Products](#)