

Watertight Devices, Twist-Lock® Receptacle with Lift Cover, 15A, 125VAC, 2 Pole, 3 Wire, Thermoplastic elastomer, NEMA L5- 15R, Yellow.

By Hubbell Wiring Device-Kellems
Catalog # [HBL65W47](#)



Watertight Devices, Twist-Lock® Receptacle with Lift Cover,
15A, 125VAC, 2 Pole, 3 Wire, Thermoplastic elastomer, NEMA L5-
15R, Yellow.

Performance

- Electrical - Current Interrupting - Rated for current interruption per UL498
- Electrical - Dielectric Voltage - 2500V AC
- Electrical - Max Working Voltage - As marked
- Electrical - Temperature Rise - 30°C max per UL498 at rated current
- Environmental - UV resistance - All exposed materials are UV stabilized
- Environmental - Moisture Resistance - UL Listed 4, 4X, 12, 6, 6P
- Environmental - Operating Temperatures - -40°C (without impact) to +60°C continuous

General

Catalog Number	HBL65W47
Color	Yellow
EU RoHS Indicator	Contact Manufacturer
Item Type	15A Watertight Twist-Lock® Receptacle
Number Of Poles	2-Pole
Type	Receptacle
UPC	783585456614

Dimensions

Dimensions	4.56 in x 3.10 in x 2.66 in
Height	2.66 in
Length	4.56 in

Width 3.1 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• IP69K In Use• Meets NEMA WD-1, WD-6 And ANSI Standards
Nema Rating	L5-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5
Pallet Quantity	810

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL65W47](#)
[Warranty - Industrial & Commercial Products](#)