

## Watertight Devices, Twist-Lock® Receptacle with Lift Cover, 20A, 250VAC, 2 Pole, 3 Wire, Thermoplastic elastomer, NEMA L6- 20R, Yellow.

By Hubbell Wiring Device-Kellems  
Catalog # [HBL67W48](#)



Watertight Devices, Twist-Lock® Receptacle with Lift Cover,  
20A, 250VAC, 2 Pole, 3 Wire, Thermoplastic elastomer, NEMA  
L6-20R, Yellow.

### Performance

- Electrical - Current Interrupting - Rated for current interruption per UL498
- Electrical - Dielectric Voltage - 2500V AC
- Electrical - Max Working Voltage - As marked
- Electrical - Temperature Rise - 30°C max per UL498 at rated current
- Environmental - UV resistance - All exposed materials are UV stabilized
- Environmental - Moisture Resistance - UL Listed 4, 4X, 12, 6, 6P
- Environmental - Operating Temperatures - -40°C (without impact) to +60°C continuous

### General

Catalog Number	HBL67W48
Color	Yellow
EU RoHS Indicator	Contact Manufacturer
Item Type	20A Watertight Twist-Lock® Receptacle
Number Of Poles	2-Pole
Type	Receptacle
UPC	783585433158

### Dimensions

Dimensions	4.56 in x 3.10 in x 2.92 in
Height	2.92 in
Length	4.56 in

Width 3.1 in

### Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	250 V
Voltage Rating Description	250 V

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• IP69K In Use</li><li>• Meets NEMA WD-1, WD-6 And ANSI Standards</li></ul>
Nema Rating	L6-20R
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	5
Pallet Quantity	765

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL67W48](#)  
[Warranty - Industrial & Commercial Products](#)