

# Watertight Devices, Twist-Lock® Receptacle with Lift Cover, 30A, 3 Phase 480V AC, 3 Pole, 4 Wire, Thermoplastic elastomer, NEMA L16-30R, Yellow



By Hubbell Wiring Device-Kellems  
Catalog # [HBL69W76](#)

Watertight Devices, Twist-Lock® Receptacle with Lift Cover,  
30A, 3 Phase 480V AC, 3 Pole, 4 Wire, Thermoplastic elastomer,  
NEMA L16-30R, Yellow

## Performance

- Electrical - Current Interrupting - Rated for current interruption per UL498
- Electrical - Dielectric Voltage - 2500V AC
- Electrical - Max Working Voltage - As marked
- Electrical - Temperature Rise - 30°C max per UL498 at rated current
- Environmental - UV resistance - All exposed materials are UV stabilized
- Environmental - Moisture Resistance - UL Listed 4, 4X, 12, 6, 6P
- Environmental - Operating Temperatures - -40°C (without impact) to +60°C continuous

## General

Catalog Number	HBL69W76
Color	Yellow
EU RoHS Indicator	Contact Manufacturer
Item Type	30A Watertight Twist-Lock® Receptacle
Number Of Poles	3-Pole
Type	Receptacle
UPC	783585433295

## Dimensions

Dimensions	4.56 in x 3.10 in x 2.92 in
Height	2.92 in
Length	4.56 in

Width 3.1 in

## Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Voltage Rating	3 Phase 480 VAC
Voltage Rating Description	3 Phase 480 VAC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>IP69K In Use</li><li>Meets NEMA WD-1, WD-6 And ANSI Standards</li></ul>
Nema Rating	L16-30R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	5
Pallet Quantity	765

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL69W76](#)  
[Warranty - Industrial & Commercial Products](#)