



Wiring Device-Kellems

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 6) Receptacles, Metallic Body, 1050 Joules, 6' Cord

By Hubbell Wiring Device-Kellems
Catalog # [HBL6MPS1050](#)



Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 6) Receptacles, Metallic Body, 1050 Joules, 6' Cord

Application

Standard Devices

General

| | |
|------------------------------|--|
| Color | Office White |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Indicator(s) Type | LED Indicator |
| Item Type | Surge Protection Plug Strips |
| Material | Steel |
| Material - Mounting Hardware | Portable |
| Number Of Outlets | 6 |
| Operating Temperature | 32 Deg F to 140 Deg F (0 Deg C to 60 Deg C) |
| Outlet | Straight Blade 5-15R |
| Performance | <ul style="list-style-type: none"> • Electrical - Max Surge Current - 19.5kA • Electrical - Max. Operating Voltage - 130 • Electrical - Operating Frequency - 50/60Hz • Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C) |
| Response Time | 5 |
| Series | Economy Surge Strips |
| Type | Metallic |
| UPC | 783585120676 |

Dimensions

Display Size 1050 Joules

Electrical Ratings

| | |
|---------------------------|--------------|
| Connectivity | Plug-In |
| Current / Amperage Rating | 15 A |
| Current Rating | 15 A |
| Frequency Rating | 60 Hz |
| Phase | Single Phase |

Conductor Related

Cord Length 6 ft

Logistics

Carton Quantity 20

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Surge Plug Strips](#)



A proud member of the Hubbell Family.