

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 6 Outlet with Telephone/Fax, 6' Cord, Office White

By Hubbell Wiring Device-Kellems
Catalog # [HBL6PS1050MA](#)



Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A
125V, 6 Outlet with Telephone/Fax, 6' Cord, Office White

General

Application	6 Outlet, Standard Devices
Catalog Number	HBL6PS1050MA
Color	Office White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Non-Metallic
Material - Mounting Hardware	Portable
Number Of Outlets	6
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Performance	Electrical - Max Surge Current - 19.5kA Electrical - Max. Operating Voltage - 130 Electrical - Operating Frequency - 50/60Hz Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C)
Response Time	5
Series	Economy Surge Strips
Type	Non-Metallic Non-Metallic
UPC	783585120546

Dimensions

Display Size	1050 Joules
--------------	-------------

Electrical Ratings

Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase

Conductor Related

Cord Length	6 ft
-------------	------

Logistics

Carton Quantity	1
Pallet Quantity	480

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Warranty - Surge Plug Strips](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL6PS1050MA-SPEC-EN | REV 6/2024