

Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Angled, 4-Pole 4-Wire Non-Grounding, 60A 3 Phase 120/208V AC, 18-60P

By Hubbell Wiring Device-Kellems
Catalog # [HBL7302C](#)



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Angled, 4-Pole 4-Wire Non-Grounding, 60A 3 Phase 120/208V AC, 18-60P, Black, Single Pack.

Features

- Heavy Duty
- Industrial/Commercial Grade
- Angled

General

Catalog Number	HBL7302C
Color	Black
Cord Range	0.625"-1.310"
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	7.5
Material	Nylon
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Style	Non-Grounding
Type	Plug
UPC	783585015378

Dimensions

Dimensions	4.13 in x 2.88 in x 2.88 in
Height	2.88 in
Length	4.13 in
Weight	0.8 lb
Width	2.88 in

Electrical Ratings

Amperage Rating	60 A
Current / Amperage Rating	60 A
Current Rating	60 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	120/208 VAC
Voltage Rating Description	3 Phase 120/208 VAC

Conductor Related

Number Of Wires	4-Wire
-----------------	--------

Certifications And Compliance

Industry Standard(s)	UL Listed, File E2186, Listed To UL Standard 498
Nema Rating	18-60P

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - HBL7302C](#)
- [Warranty - Industrial & Commercial Products](#)