

**HUBBELL**  
Wiring Device-Kellems

**Locking Devices, Midget Twist-Lock®, Valise®, Male Plug, 15A  
125V, 2-Pole 2-Wire Non Grounding,  
NEMA ML-1P, Screw Terminal, Black.**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL7465V](#)

Locking Devices, Midget Twist-Lock®, Valise®, Male Plug, 15A  
125V, 2-Pole 2-Wire Non Grounding, NEMA ML-1P, Screw  
Terminal, Black.



## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accomodation - #18 AWG - #14 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

## General

Catalog Number	HBL7465V
Cord Range	0.220"-0.385"(5.6-9.8)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Midget Twist-Lock® Valise® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Blades - Brass</li><li>• Body Holding Screws - Steel - Zinc plated</li><li>• Housing - Nylon</li><li>• Terminal Clamps - Steel - Nickel plated</li><li>• Terminal Screws - #6 - 32 Steel (Philips / Slotted / Robertson)</li></ul>
Type	Plugs
UPC	783585237282

## Dimensions

Dimensions	1.25 in x 1.06 in x 1.06 in
Display Size	Midget Locking
Height	1.06 in
Length	1.25 in
Weight	0.05 lb
Width	1.06 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Cable Range	0.220 - 0.385 in
Cord Type	All Listed Portables
Number Of Wires	2-Wire
Wire Size	#18 AWG to #14 AWG

## Certifications And Compliance

Industry Standard(s)	Fed.Spec.W-C-596
Nema Rating	ML-1P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	8400

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL7465V](#)  
[Warranty - Industrial & Commercial Products](#)

