

HUBBELL
Wiring Device-Kellems

Locking Devices, Midget Twist-Lock®, Industrial, Flanged Inlet, 15A 125V AC, 2-Pole 2-Wire Non Grounding, NEMA ML-1P, Stainless Steel Flange

By Hubbell Wiring Device-Kellems
Catalog # [HBL7466](#)

Locking Devices, Midget Twist-Lock®, Industrial, Flanged Inlet, 15A 125V AC, 2-Pole 2-Wire Non Grounding, NEMA ML-1P, Screw Terminal, Stainless Steel Flange, Non-Polarized.



Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18 AWG - #14 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL7466
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Midget Twist-Lock® Flanged Inlet
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Base - Phenolic• Blades - Brass• Flange - Stainless Steel• Terminal Screws - #5-40 Brass
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Flanged Inlet
UPC	783585237312

Dimensions

Dimensions	1.63 in x 1.63 in x 0.94 in
Display Size	Midget Locking
Height	0.94 in
Length	1.63 in
Weight	0.05 lb
Width	1.63 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	2-Wire
Wire Size	#18 AWG to #14 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Listed to UL 498
Nema Rating	ML-1P

Logistics

Carton Quantity	10
Pallet Quantity	5000

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL7466](#)
[Warranty - Industrial & Commercial Products](#)

