



Locking Devices, Midget Twist-Lock®, Industrial, Flanged Receptacle, 15A 125V AC, 2-Pole 2-Wire Non Grounding, NEMA ML-1R, Stainless Steel Flange.

By Hubbell Wiring Device-Kellems
Catalog # [HBL7468](#)



Locking Devices, Midget Twist-Lock®, Industrial, Flanged Receptacle, 15A 125V AC, 2-Pole 2-Wire Non Grounding, NEMA ML-1R, Screw Terminal, Stainless Steel Flange.

Features

- Stainless Steel mounting flange
- High heat resistant phenolic base

Application

Heavy Duty Industrial

General

| | |
|------------------------------|---|
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Insulation | Insulated Body |
| Item Type | 15A Midget Twist-Lock® Flanged Receptacle |
| Material | Nylon |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| Operating Temperature | Maximum continuous 75°C and minimum -40°C without Impact |
| Performance | <ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17 • Environmental - Moisture Resistance - IP20 Suitability • Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact) • Mechanical - Terminal Accommodation - #18 AWG - #14 AWG solid or stranded copper wire only. • Mechanical - Terminal Identification - Terminals identified by color |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 1.63 in x 1.63 in x 0.78 in |
| Display Size | Midget Locking |
| Height | 0.78 in |
| Length | 1.63 in |
| Weight | 0.05 lb |
| Width | 1.63 in |

Electrical Ratings

| | |
|----------------------------|---------------------------|
| Amperage Rating | 15 A |
| Connectivity | Screw Terminals |
| Current / Amperage Rating | 15 A |
| Current Rating | 15 A |
| Dielectric Strength | Withstands 2,000V minimum |
| Phase | Single Phase |
| Voltage Rating | 125 V |
| Voltage Rating Description | 125 V |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 2-Wire |
| Wire Size | #18 AWG to #14 AWG |

Certifications and Compliance

| | |
|------------------------------------|--|
| Industry Standard(s) | <ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Listed to UL 498 |
| Nema Rating | ML-1R |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

Identified in accordance with UL 498

| | |
|--------------------|---|
| Temperature Rating | Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact. |
| Type | <ul style="list-style-type: none">• Flanged Receptacle• Flanged Receptacle |
| UPC | 783585237336 |



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL7468-SPEC-EN | REV 1/2024