



Locking Devices, Midget Twist-Lock®, Industrial, Female Valise® Connector, 15A 125/250V AC, 3-Pole 3-Wire Non Grounding, NEMA ML-3R

By Hubbell Wiring Device-Kellems
Catalog # [HBL7484V](#)



Locking Devices, Midget Twist-Lock®, Industrial, Female Valise® Connector, 15A 125/250V AC, 3-Pole 3-Wire Non Grounding, NEMA ML-3R, With Insulation Displacement Terminal, Black.

Features

- Fully insulated, abuse resistant nylon housing
- Insulation displacement terminals reduce wiring time
- Insulation displacement terminal

Application

Heavy Duty Industrial

General

Color	Black
Cord Range	0.300"-0.430"(7.6-10.9)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Midget Twist-Lock® Valise® Connector
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none">• Electrical - Current Interrupting - Certified for current interrupting at full rated current• Electrical - Dielectric Voltage - Withstands 2,000V minimum• Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17• Environmental - Moisture Resistance - IP20 Suitability• Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)• Mechanical - Terminal Accomodation - #18 AWG - #14 AWG stranded copper

Dimensions

Dimensions	1.19 in x 1.19 in x 1.98 in
Display Size	Midget Locking
Height	1.98 in
Length	1.19 in
Weight	0.10 lb
Width	1.19 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Insulation Displacement
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V

Conductor Related

Cable Range	0.300 - 0.430 in
Conductor Range	#14 AWG to #12 AWG
Number Of Wires	3-Wire
Wire Size	#18 AWG to #14 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Listed to UL 498
----------------------	---

Nema Rating	ML-3R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

	wire only.
	<ul style="list-style-type: none">• Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	<ul style="list-style-type: none">• Connector Body
	<ul style="list-style-type: none">• Connector Body
UPC	783585237398



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL7484V-SPEC-EN | REV 1/2024