

**HUBBELL**  
Wiring Device-Kellems

**Locking Devices, Midget Twist-Lock®, Industrial, Male Plug, 15A 125/250V AC, 3-Pole 3-Wire Non Grounding, NEMA ML-3P, Screw Terminal, Black.**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL7485](#)

Locking Devices, Midget Twist-Lock®, Industrial, Male Plug, 15A 125/250V AC, 3-Pole 3-Wire Non Grounding, NEMA ML-3P, Screw Terminal, Black.



## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accomodation - #18 AWG - #14 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

## General

Catalog Number	HBL7485
Cord Range	0.281"-0.421"(7.1-10.7)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Midget Twist-Lock® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Blade Holder - Phenolic</li><li>• Blades - Brass</li><li>• Housing - Nylon</li><li>• Terminal Clamp - Zinc plated steel with black lacquer finish</li><li>• Terminal Screws - #5-40 Brass</li></ul>
Type	Plugs
UPC	783585237411

## Dimensions

Dimensions	1.17 in x 1.17 in x 2.45 in
Display Size	Midget Locking
Height	2.45 in
Length	1.17 in
Weight	0.05 lb
Width	1.17 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V

## Conductor Related

Cable Range	0.300 - 0.430 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#18 AWG to #14 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA C22.2 No.42</li><li>• Listed to UL 498</li></ul>
Nema Rating	ML-3P

## Logistics

Carton Quantity	10
Pallet Quantity	6000

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL7485](#)  
[Warranty - Industrial & Commercial Products](#)

