

HUBBELL
Wiring Device-Kellems

Locking Devices, Midget Twist-Lock®, Industrial, Flanged Receptacle, 15A 125/250V AC, 3-Pole 3-Wire Non Grounding, NEMA ML-3R Nylon Flange.

By Hubbell Wiring Device-Kellems
Catalog # [HBL7487N](#)

Locking Devices, Midget Twist-Lock®, Industrial, Flanged Receptacle, 15A 125/250V AC, 3-Pole 3-Wire Non Grounding, NEMA ML-3R, Screw Terminal, Black Nylon Flange.



Application

Heavy Duty Industrial

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18 AWG - #14 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL7487N
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Midget Twist-Lock® Flanged Receptacle
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Base - Nylon• Blades - Bronze• Flange - Nylon• Terminal Screws - #5-40 Brass
Type	Flanged Receptacle
UPC	783585237473

Dimensions

Dimensions	2.06 in x 1.75 in x 0.92 in
Display Size	Midget Locking Devices
Height	0.92 in
Length	2.06 in
Weight	0.05 lb
Width	1.75 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #14 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Listed to UL 498
Nema Rating	ML-3R

Logistics

Carton Quantity	10
Pallet Quantity	4500

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL7487N](#)
[Warranty - Industrial & Commercial Products](#)

