

# Locking Devices, Twist-Lock®, Industrial, Duplex Receptacle, 15A 125V, 2-Pole 2-Wire Non Grounding, L1-15R, Screw Terminal, Black

By Hubbell Wiring Device-Kellems  
Catalog # [HBL7540](#)



Twist-Lock® Industrial Duplex Flush Receptacle, 15A 125V, 2-Pole  
2-Wire Non Grounding, NEMA L1-15R, Screw Terminal

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18 AWG - #10 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

## General

|                              |  |
|------------------------------|--|
| Catalog Number               | HBL7540  |
| EU RoHS Indicator            | No   |
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means  |
| Horsepower - Maximum         | 0.5  |
| Item Type                    | 15A Non-Grounding Duplex Flush Receptacle  |
| Material                     | Thermoplastic  |
| Material - Mounting Hardware | Screw Mounting   |
| Number Of Poles              | 2-Pole   |
| Operating Temperature        | Maximum continuous 75°C and minimum -40°C without Impact   |
| Specifications               | <ul style="list-style-type: none"><li>• Contacts - Brass</li><li>• Housing - Molded Thermoset</li><li>• Mounting Screw - Steel-zinc-plated</li><li>• Terminal Screws - Brass</li></ul> |
| Type                         | Receptacle   |
| UPC                          | 783585237602   |

## Dimensions

|              |                             |
|--------------|-----------------------------|
| Dimensions   | 3.28 in x 1.32 in x 1.19 in |
| Display Size | Standard Sized Product      |
| Height       | 1.19 in                     |
| Length       | 3.28 in                     |
| Weight       | 0.25 lb                     |
| Width        | 1.32 in                     |

## Electrical Ratings

|                            |                           |
|----------------------------|---------------------------|
| Amperage Rating            | 15 A                      |
| Connectivity               | Screw Terminals           |
| Current / Amperage Rating  | 15 A                      |
| Current Rating             | 15 A                      |
| Dielectric Strength        | Withstands 2,000V minimum |
| Phase                      | Single Phase              |
| Voltage Rating             | 125 V                     |
| Voltage Rating Description | 125 V                     |

## Conductor Related

|                 |                    |
|-----------------|--------------------|
| Number Of Wires | 2-Wire             |
| Wire Size       | #18 AWG to #10 AWG |

## Certifications And Compliance

|                      |   |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"><li>• Certified to CSA C22.2 No.42</li><li>• Listed to UL 498</li></ul> |
| Nema Rating          | L1-15R  |

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL7540](#)  
[Warranty - Industrial & Commercial Products](#)