

Locking Devices, Midget Twist-Lock®, Industrial, Male Plug, 15A 125V, 2-Pole 2-Wire Non Grounding, L1-15P, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL7545C](#)

Locking Devices, Midget Twist-Lock®, Industrial, Male Plug, 15A 125V, 2-Pole 2-Wire Non Grounding, L1-15P, Screw Terminal, Black and White.



Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18 AWG - #10 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL7545C
Cord Range	0.230"-0.720"(5.8-18.3)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> • Assembly Screws - Steel - nickel plated • Blades - Brass • Housing / Cord Clamp - Nylon • Terminal Clamp - Cold rolled steel - nickel plated • Terminal Retainer - Clear polycarbonate • Terminal Screws - #8-32 Brass (Phillips / Slotted /

Type	Robertson)
UPC	Plugs 783585178509

Dimensions

Dimensions	1.96 in x 1.52 in x 1.52 in
Display Size	Standard Sized
Height	1.52 in
Length	1.96 in
Weight	0.15 lb
Width	1.52 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Cable Range	0.230 - 0.720 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No. 42 • Fed. Spec W-C-596 • Listed to UL 498
Nema Rating	L1-15P
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity 10
Pallet Quantity 3600

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL7545C](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL7545C-SPEC-EN | REV 10/2024