

HUBBELL
Wiring Device-Kellems

**Locking Devices, Midget Twist-Lock®, Industrial, Male Plug, 15A
125V AC, 2-Pole 3-Wire Grounding,
NEMA ML-2P**

By Hubbell Wiring Device-Kellems
Catalog # [HBL7594](#)

Locking Devices, Midget Twist-Lock®, Industrial, Male Plug, 15A
125V AC, 2-Pole 3-Wire Grounding, NEMA ML-2P, Screw
Terminal, Black nylon cover, phenolic body, multiple drive screw
terminals



Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accomodation - #18 AWG - #14 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL7594
Cord Range	0.281"-0.421"(7.1-10.7)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Midget Twist-Lock® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Blade Holder - Phenolic• Blades - Brass• Housing - Nylon• Terminal Clamp - Zinc plated steel with black lacquer finish• Terminal Screws - #5-40 Brass
Type	Plugs
UPC	783585237770

Dimensions

Dimensions	1.17 in x 1.17 in x 2.45 in
Display Size	Midget Locking
Height	2.45 in
Length	1.17 in
Weight	0.1 lb
Width	1.17 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Cable Range	0.300 - 0.430 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#18 AWG to #14 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Listed to UL 498
Nema Rating	ML-2P

Logistics

Carton Quantity	10
Pallet Quantity	12000

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL7594](#)
[Warranty - Industrial & Commercial Products](#)

