

Wallplates and Boxes, Weatherproof Covers, 1-Gang, 1) 50A Twist-Lock® Opening, Standard Size, Cast Aluminum

By Hubbell Wiring Device-Kellems
Catalog # [HBL7770](#)



Wallplates and Boxes, Weatherproof Covers, 1-Gang, 1) 50A
Twist-Lock® Opening, Standard Size, Cast Aluminum

General

Catalog Number	HBL7770
Construction	Cast
EU RoHS Indicator	Yes
Item Type	Weatherproofing Covers
Knockouts	None
Material	Aluminum, Cast
Material - Mounting Hardware	Vertical FS/FD Mount- Mounting Screws
Number Of Outlets	1-Device
Number of Gang(s)	1-Gang
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Gasket - Neoprene• Material - Aluminum• Rivet - Aluminum• Spring - Stainless steel
Style	For 50A Twist-Lock® Single Receptacle
Type	Covers
UPC	783585809519

Dimensions

Dimensions	2.84 in x 2.18 in x 4.18 in
Height	4.18 in
Length	2.84 in
Weight	0.75 lb
Width	2.18 in

Electrical Ratings

Dielectric Strength	Withstands 2,000V minimum
---------------------	---------------------------

Certifications And Compliance

Industry Standard(s)	UL Listed - Canadian and U.S.
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	810

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL7770](#)
[Warranty - Industrial & Commercial Products](#)