

## Switches and Lighting Control, Motor Disconnect, 2-Pole, 30A 600V, Back and Side Wired

By Hubbell Wiring Device-Kellems  
Catalog # [HBL7832D](#)



Switches and Lighting Control, Motor Disconnect, 2-Pole, 30A  
600V, Back and Side Wired

### General

|                              |   |
|------------------------------|---|
| Catalog Number               | HBL7832D  |
| EU RoHS Indicator            | Yes   |
| Environmental Conditions     | Indoor Dry Unless Protected By<br>Additional Means          |
| Horsepower - Maximum         | 15  |
| Item Type                    | Standard Toggle   |
| Load Capacity                | Inductive   |
| Material                     | Stainless Steel   |
| Material - Mounting Hardware | Screw Mounting  |
| Number Of Poles              | 2 Pole  |
| Operating Cycles             | 10,000 Cycles Minimum                                       |
| Operating Temperature        | Maximum continuous 75°C and<br>minimum -40°C without Impact |
| Series                       | Standard Toggle   |
| Type                         | Back & Side Wire  |
| UPC                          | 783585202815  |

### Dimensions

Display Size  
Weight

Standard Sized Product  
0.45 lb

### Electrical Ratings

|                            |                     |
|----------------------------|---------------------|
| Amperage Rating            | 30 A                |
| Connectivity               | Back and Side Wired |
| Current / Amperage Rating  | 30 A                |
| Current Rating             | 30 A                |
| Phase                      | Single Phase        |
| Voltage Rating             | 600 VAC             |
| Voltage Rating Description | 600 VAC             |
| Wattage                    | 18000 W             |

### Logistics

Carton Quantity 10

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL7832D](#)