



Wiring Device-Kellems

# Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Straight, 3-Pole 3-Wire Non Grounding, 50A 125/250V, 10-50P, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # [HBL7977](#)



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Straight, 3-Pole 3-Wire Non Grounding, 50A 125/250V, 10-50P, Black, Single Pack.

## General

Color	<ul style="list-style-type: none"> <li>• Black</li> <li>• Noir</li> </ul>
Cord Range	0.625"-1.187"
Horsepower - Maximum	3
Material	Nylon
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Style	Non-Grounding
Type	Plug
UPC	783585015132

## Dimensions

Dimensions	4.33 in x 2.75 in x 1.88 in
Height	1.88 in
Length	4.33 in
Weight	0.55 lb
Width	2.75 in

## Electrical Ratings

Amperage Rating	50 A
Current / Amperage Rating	50 A
Current Rating	50 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Certifications and Compliance

Industry Standard(s)	UL Listed, File E2186, Listed To UL Standard 498
Nema Rating	10-50P

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBL7977-SPEC-EN | REV 1/2024