



# Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 7 Outlet, 150 Joules, 6' Cord, Office White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL7PS1050A](#)



Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 7 Outlet, 150 Joules, 6' Cord, Office White

## Application

7 Outlet, Standard Devices

## General

Color	<ul style="list-style-type: none"> <li>Office White</li> <li>Blanc cassé</li> </ul>
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Non-Metallic
Material - Mounting Hardware	Portable
Number Of Outlets	7
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Performance	<ul style="list-style-type: none"> <li>Electrical - Max Surge Current - 19.5kA</li> <li>Electrical - Max. Operating Voltage - 130</li> <li>Electrical - Operating Frequency - 50/60Hz</li> <li>Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C)</li> </ul>
Response Time	5
Series	Economy Surge Strips
Type	<ul style="list-style-type: none"> <li>Non-Metallic</li> <li>Non-Metallic</li> </ul>
UPC	783585120553

## Dimensions

Display Size 1050 Joules

## Electrical Ratings

Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase

## Conductor Related

Cord Length 6 ft

## Logistics

Carton Quantity 10

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Surge Plug Strips](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBL7PS1050A-SPEC-EN | REV 1/2024