

**HUBBELL**  
Wiring Device-Kellems

**Straight Blade Devices,  
Receptacles, Duplex, Tamper  
Resistant Hospital Grade, 2-Pole 3-  
Wire Grounding, 15A 125V, 5-15R,  
Red, Single Pack**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL8200SGRA](#)

Straight Blade Devices, Receptacles, Duplex, Tamper Resistant  
Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Red,  
Single Pack.



## General

Application	Extra Heavy Duty Hospital Grade
Catalog Number	HBL8200SGRA
Color	Red
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current  Electrical - Dielectric Voltage - Withstands 2,000V minimum  Environmental - Flammability - UL 94V-0 and UL 94-5 VA  Environmental - IP Suitability - IP20  Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)  Mechanical - Ground Terminal Accommodation - #12-#10 AWG stranded or solid copper wire only  Mechanical - Product Identification - Ratings are a permanent part of the device  Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
Series	Hospital Grade
Style	Tamper Resistant
Type	Receptacle
UPC	783585152257

## Dimensions

Dimensions	3.29 in x 1.65 in x 1.27 in
Display Size	Standard Sized Product
Height	1.27 in
Length	3.29 in
Weight	0.35 lb
Width	1.65 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Wire Leads
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	CSA Certified, C22.2, No. 42 File 285  Fed. Spec. W-C-596  NEMA® WD-6 Compliant  UL Listed to UL498 File No. E2186
Nema Rating	5-15R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Warranty - Industrial & Commercial Products](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL8200SGRA-SPEC-EN | REV 6/2024