



Straight Blade Devices, Male Plug, Insulgrip, Hospital Grade, Angled, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Transparent, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL8215CAT](#)



Straight Blade Devices, Male Plug, Insulgrip, Hospital Grade, Angled, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Transparent, Single Pack

Features

- Individual wiring terminals completely enclosed
- Powerful, offsetting cord grips clamp on individual conductors
- Transparent for easy visual inspection of termination

Application

Hospital Grade

General

Color	Transparent
Cord Range	0.250"-0.655" (6.4-16.6)
Horsepower - Maximum	0.5
Item Type	Insulgrip Plug
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2000V AC minimum
- Environmental - Flammability - UL 94 HB or better
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #18-10 AWG
- Mechanical - Terminal Identification - Terminals identified in accordance

Dimensions

Height	2.11 in
Thickness	1.22
Weight	0.15 lb
Width	1.53 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 File 285 • Fed. Spec. W-C-596 • UL Listed to UL498 File E1706
----------------------	---

Nema Rating	5-15P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Literature - Healthcare Product Solutions](#)
[Warranty - Industrial & Commercial Products](#)

Identified in accordance
with UL 498 and CSA

Series	Hospital Grade
Style	Insulgrip
Type	<ul style="list-style-type: none">• Plug• Plug
UPC	783585179254



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL8215CAT-SPEC-EN | REV 1/2024