

HUBBELL
Wiring Device-Kellems

Straight Blade Devices, Female Connector, Insulgrip, Hospital Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Black and White, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL8219C](#)

Straight Blade Devices, Female Connector Body, Insulgrip, Hospital Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Black and White, Single Pack, Canadian Version.



General

| | |
|------------------------------|---|
| Application | |
| Catalog Number | HBL8219C |
| Color | Black and White |
| Cord Range | 0.230"-0.720" (5.8-18.3) |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Horsepower - Maximum | 0.5 |
| Insulation | Insulated Body |
| Item Type | Insulgrip Connector |
| Material | Nylon |
| Material - Mounting Hardware | Cord Mounted |
| Number Of Poles | 2-Pole |
| Operating Temperature | Maximum continuous 75°C and minimum -40°C without Impact |
| Performance | Electrical - Current Interrupting - Certified for current interrupting at full rated current |
| | Electrical - Dielectric Voltage - Withstands 2000V AC minimum |
| | Environmental - Flammability - UL 94 HB or better |
| | Environmental - IP Suitability - IP20 |
| | Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) |
| | Mechanical - Product Identification - Ratings are a permanent part of the device |
| | Mechanical - Terminal Accommodation - #18-10 AWG |
| | Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA |
| Series | Hospital Grade |
| Style | Insulgrip |
| Temperature Rating | Max Continuous- 75 Degrees C, Minimum- -40 Without Impact |
| Type | Connector Body |
| | Connector Body |
| UPC | 783585179506 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 2.78 in x 1.53 in x 1.53 in |
| Display Size | Standard |
| Height | 1.53 in |
| Length | 2.78 in |
| Weight | 0.2 lb |
| Width | 1.53 in |

Electrical Ratings

| | |
|----------------------------|---------------------------|
| Amperage Rating | 15 A |
| Connectivity | Screw Terminals |
| Current / Amperage Rating | 15 A |
| Current Rating | 15 A |
| Dielectric Strength | Withstands 2,000V minimum |
| Voltage Rating | 125 V |
| Voltage Rating Description | 125 V |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #18 AWG to #10 AWG |

Certifications And Compliance

| | |
|------------------------------------|--|
| Industry Standard(s) | Certified to CSA, C22.2, No. 42 File 285 |
| | Fed. Spec. W-C-596 |
| | UL Listed to UL498 File No. E2186 |
| Nema Rating | 5-15R |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------|------|
| Carton Quantity | 10 |
| Pallet Quantity | 6600 |

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Healthcare Product Solutions](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL8219C-SPEC-EN | REV 6/2024