

Straight Blade Devices, Receptacles, 4-Pole 4-Wire non Grounding receptacles and plugs, 30A 3 Phase,120/208 V, 18-30R, Black, Single Pack.

By Hubbell Wiring Device-Kellems
Catalog # [HBL8330A](#)



Straight Blade Devices, Receptacles, 4-Pole 4-Wire non Grounding receptacles and plugs, 30A 3 Phase,120/208 V, 18-30R, Black, Single Pack.

Application

Heavy Duty

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-0
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12 AWG through #4 AWG copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL8330A
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	3
Item Type	Single
Material	Thermoplastic/Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> • Box Terminals - Copper • Contacts - Brass • Ground Shunt - Brass • Housing - Reinforced Thermoplastic Polyester • Mounting Plate - .062 in. (1.5) Pre-Plated steel

Type
UPC

Receptacle
783585015453

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Weight	0.6 lb
Width	2.75 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	120/208 VAC
Voltage Rating Description	120/208 VAC
Wattage	6240 W

Conductor Related

Number Of Wires	4-Wire Non-Grounding
Wire Size	#12 AWG to #6 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA • NEMA® WD-6 Compliant • UL Listed File E2186
Nema Rating	18-30R

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalogs - WDK Catalog Full 2024](#)



A Hubbell brand