

Straight Blade Devices, Plug Industrial Grade, 3-Pole 4-Wire Grounding, 30A 3 Phase 250V AC, 15-30P, Single Pack.

By Hubbell Wiring Device-Kellems
Catalog # [HBL8431C](#)



Straight Blade Devices, Plug Industrial Grade, 3-Pole 4-Wire
Grounding, 30A 3 Phase 250V AC, 15-30P, Single Pack.

Performance

- Electrical: Current Interrupting: Certified for current interrupting at full rated current
- Dielectric Voltage : Withstands 2,000V minimum
- Mechanical: Terminal Accommodation: #12 AWG through #4 AWG copper wire only
- Terminal Identification :Terminals identified in accordance with UL 498 and CSA
- Environmental: Flammability: UL 94 HB
- IP Suitability: IP20
- Operating Temperatures: Maximum continuous 75°C
- minimum -40°C (w/o impact)

General

Catalog Number	HBL8431C
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Style	Grounding
Type	Plug
UPC	783585015408

Dimensions

Weight	0.8 lb
--------	--------

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	250 VAC
Voltage Rating Description	250 V

Conductor Related

Number Of Wires	4-Wire
Wire Size	#12 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• UL Listed File E1706• Certified to CSA
Nema Rating	15-30P

Logistics

Carton Quantity	5
Pallet Quantity	765

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL8431C](#)
[Warranty - Industrial & Commercial Products](#)