

## Straight Blade Devices, Receptacles, Industrial Grade, 2- Pole 3-Wire Grounding, 30A 125V, 5-30R, Black RTP, Single Pack.

By Hubbell Wiring Device-Kellems  
Catalog # [HBL9308](#)



Straight Blade Devices, Receptacles, Industrial Grade, 2-Pole 3-  
Wire Grounding, 30A 125V, 5-30R, Black RTP, Single Pack.

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-0
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12 AWG through #4 AWG copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

### General

|                              |  |
|------------------------------|--|
| Catalog Number               | HBL9308  |
| Color                        | Black  |
| EU RoHS Indicator            | Yes  |
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means  |
| Horsepower - Maximum         | 2  |
| Item Type                    | Single   |
| Material - Mounting Hardware | Screw Mounting   |
| Number Of Poles              | 2-Pole   |
| Operating Temperature        | Maximum continuous 75°C and minimum -40°C without Impact   |
| Series                       | Extra Heavy Duty   |
| Specifications               | <ul style="list-style-type: none"><li>• Box Terminals - Copper</li><li>• Contacts - Brass</li><li>• Ground Shunt - Brass</li><li>• Housing - Reinforced Thermoplastic Polyester</li><li>• Mounting Plate - .062 in. (1.5) Pre-Plated Steel</li></ul> |
| Style                        | Grounding  |
| Type                         | Receptacle   |
| UPC                          | 783585015217   |

### Dimensions

|              |                        |
|--------------|------------------------|
| Display Size | Standard Sized Product |
| Weight       | 0.45 lb                |
| Width        | 2.23 in                |

### Electrical Ratings

|                            |                                     |
|----------------------------|-------------------------------------|
| Amperage Rating            | 30 A                                |
| Connectivity               | Back and Side Wired Screw Terminals |
| Current / Amperage Rating  | 30 A                                |
| Current Rating             | 30 A                                |
| Dielectric Strength        | Withstands 2,000V minimum           |
| Phase                      | Single Phase                        |
| Voltage Rating             | 125 V                               |
| Voltage Rating Description | 125 V                               |
| Wattage                    | 3750 W                              |

### Conductor Related

|                 |                   |
|-----------------|-------------------|
| Number Of Wires | 3-Wire            |
| Wire Size       | #12 AWG to #4 AWG |

### Certifications And Compliance

|                             |   |
|-----------------------------|---|
| Industry Standard(s)        | <ul style="list-style-type: none"><li>• CSA Certified</li><li>• NEMA® WD-6 Compliant</li><li>• UL Listed File E2186</li></ul> |
| Nema Rating                 | 5-30R   |
| Standards - RoHS Compliance | CM  |
| Status                      |   |

### Logistics

|                 |      |
|-----------------|------|
| Carton Quantity | 10   |
| Pallet Quantity | 2640 |

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL9308](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL9308-SPEC-EN | REV 1/2025