

Straight Blade Devices, Receptacles, Industrial Grade, 2- Pole 3-Wire Grounding, 30A 125V, 5-30R, Black RTP, Single Pack.

By Hubbell Wiring Device-Kellems
Catalog # [HBL9308](#)



Straight Blade Devices, Receptacles, Industrial Grade, 2-Pole 3-
Wire Grounding, 30A 125V, 5-30R, Black RTP, Single Pack.

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-0
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12 AWG through #4 AWG copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL9308
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none">• Box Terminals - Copper• Contacts - Brass• Ground Shunt - Brass• Housing - Reinforced Thermoplastic Polyester• Mounting Plate - .062 in. (1.5) Pre-Plated Steel
Style	Grounding
Type	Receptacle
UPC	783585015217

Dimensions

Display Size	Standard Sized Product
Weight	0.45 lb
Width	2.23 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	3750 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified• NEMA® WD-6 Compliant• UL Listed File E2186
Nema Rating	5-30R
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
Pallet Quantity	2640

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL9308](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL9308-SPEC-EN | REV 10/2024