

## **Straight Blade Devices, Male Plug, Nylon, 4-Position, Heavy Duty, Industrial/Commercial Grade, Angled, 2-Pole 3-Wire Grounding, 30A 250V, 6-30P.**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL9331](#)

Straight Blade Devices, Male Plug, Nylon, 4-Position, Heavy Duty, Industrial/Commercial Grade, Angled, 2-Pole 3-Wire Grounding, 30A 250V, 6-30P, Black, Single Pack.



### **Features**

- Nylon
- 4-Position
- Heavy Duty

### **Performance**

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#4 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

### **General**

|                       |   |
|-----------------------|---|
| Catalog Number        | HBL9331   |
| Color                 | Noir  |
| EU RoHS Indicator     | Contact Manufacturer  |
| Horsepower - Maximum  | 2   |
| Material              | Thermoplastic/Composite   |
| Number Of Poles       | 2-Pole  |
| Operating Temperature | Maximum continuous 75°C and minimum -40°C without Impact  |
| Series                | Extra Heavy Duty  |
| Specifications        | <ul style="list-style-type: none"><li>• Blade Holder - Reinforced Thermoplastic Polyester</li><li>• Box Terminals - Brass</li><li>• Cord Clamp - Reinforced Thermoplastic Polyester</li><li>• Housing - Supertough Nylon</li><li>• Terminal Retainer - Reinforced Thermoplastic</li></ul> |

|       |                      |
|-------|----------------------|
| Style | Polyester            |
| Type  | Grounding            |
| UPC   | Plug<br>783585015248 |

### **Dimensions**

|            |                             |
|------------|-----------------------------|
| Dimensions | 4.34 in x 2.75 in x 1.88 in |
| Height     | 1.88 in                     |
| Length     | 4.34 in                     |
| Weight     | 0.55 lb                     |
| Width      | 2.75 in                     |

### **Electrical Ratings**

|                            |                           |
|----------------------------|---------------------------|
| Amperage Rating            | 30 A                      |
| Current / Amperage Rating  | 30 A                      |
| Current Rating             | 30 A                      |
| Dielectric Strength        | Withstands 2,000V minimum |
| Voltage Rating             | 250 V                     |
| Voltage Rating Description | 250 V                     |
| Wattage                    | 7500 W                    |

### **Conductor Related**

|                 |                   |
|-----------------|-------------------|
| Number Of Wires | 3-Wire            |
| Wire Size       | #12 AWG to #4 AWG |

### **Certifications And Compliance**

|                      |   |
|----------------------|---|
| Industry Standard(s) | UL Listed to UL498 File E1706, CSA Certified to C22.2 No. 42 File 280 |
| Nema Rating          | 6-30P   |

### **Logistics**

|                 |      |
|-----------------|------|
| Carton Quantity | 10   |
| Pallet Quantity | 1360 |

### **Product Assets**



A Hubbell brand