

# Straight Blade Devices, Male Plug, Insulgrip, Heavy Duty, Industrial/Commercial Grade, Straight, 3-Pole 3-Wire Non-Grounding, 30A 125/250V, 10-30P.



By Hubbell Wiring Device-Kellems  
Catalog # [HBL9337C](#)

Straight Blade Devices, Male Plug, Insulgrip, Nylon, Heavy Duty, Industrial/Commercial Grade, Straight, 3-Pole 3-Wire Non-Grounding, 30A 125/250V, 10-30P, Black, Single Pack.

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12 AWG through #4 AWG copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

## General

Catalog Number	HBL9337C
Color	Black
Cord Range	0.625"-1.00"
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	2
Material	Nylon
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none"><li>• Blade Holder - Reinforced Thermoplastic Polyester</li><li>• Blades - Brass</li><li>• Box Terminals - Copper Alloy</li><li>• Cord Clamps - Reinforced Thermoplastic Polyester</li><li>• Housing - Supertough Nylon</li></ul>
Style	Non-Grounding
Type	Plug

UPC 783585015699

## Dimensions

Dimensions	4.13 in x 2.75 in x 2.88 in
Height	2.88 in
Length	4.13 in
Weight	0.8 lb
Width	2.75 in

## Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	<ul style="list-style-type: none"><li>• 125 V</li><li>• 250 V</li></ul>
Voltage Rating Description	125/250 V
Wattage	7500 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #4 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified</li><li>• UL Listed File E1706</li></ul>
Nema Rating	10-30P

## Logistics

Carton Quantity	5
-----------------	---

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL9337C](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL9337C-SPEC-EN | REV 10/2024