

# Straight Blade Devices, Male Plug, Nylon, Heavy Duty, Industrial/Commercial Grade, Angled, 2-Pole 3-Wire Grounding, 50A 125V, 5-50P, Single Pack.

By Hubbell Wiring Device-Kellems  
Catalog # [HBL9361](#)



Straight Blade Devices, Male Plug, Nylon, Heavy Duty,  
Industrial/Commercial Grade, Angled, 2-Pole 3-Wire Grounding,  
50A 125V, 5-50P, Black, Single Pack.

## Features

- Nylon
- Heavy Duty
- Industrial/Commercial Grade

## General

Catalog Number	HBL9361
Color	Black
Cord Range	0.625"-1.187"
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	2
Material	Nylon
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Style	Grounding
Type	Plug
UPC	783585015439

## Dimensions

Dimensions	4.34 in x 2.75 in x 1.88 in
Height	1.88 in
Length	4.34 in
Weight	0.55 lb
Width	2.75 in

## Electrical Ratings

Amperage Rating	50 A
Current / Amperage Rating	50 A
Current Rating	50 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Certifications And Compliance

Industry Standard(s)	UL Listed To UL498 File E1706, CSA Certified To C22.2 No. 42 File 280
Nema Rating	5-50P

## Logistics

Carton Quantity	10
Pallet Quantity	1360

## Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - HBL9361](#)
- [Warranty - Industrial & Commercial Products](#)