

Straight Blade Devices, Receptacles, RTP, Industrial Grade, 3-Pole 4-Wire Grounding, 60A 125/250V, 14-60R, Black, Single Pack.

By Hubbell Wiring Device-Kellems
Catalog # [HBL9460A](#)

Straight Blade Devices, Receptacles, RTP, Industrial Grade, 3-Pole 4-Wire Grounding, 60A 125/250V, 14-60R, Black, Single Pack.



Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-0
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12 AWG through #4 AWG copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL9460A
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	3
Item Type	Single
Material	Thermoplastic/Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Box Terminals - Copper• Contacts - Brass• Ground Shunt - Brass• Housing - Reinforced Thermoplastic Polyester• Mounting Plate - .062 in. (1.5) Pre-Plated Steel
Type	Receptacle
UPC	783585015347

Dimensions

Dimensions	3.28 in x 2.75 in x 2.44 in
Display Size	Standard Sized Product
Height	2.44 in
Length	3.28 in
Weight	0.6 lb
Width	2.75 in

Electrical Ratings

Amperage Rating	60 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	60 A
Current Rating	60 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	<ul style="list-style-type: none">• 125/250 V• 125 V V
Voltage Rating Description	125/250 V
Wattage	15000 W

Conductor Related

Number Of Wires	4-Wire Grounding
Wire Size	#12 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	UL, CSA, Fed Spec
Nema Rating	14-60R

Logistics

Carton Quantity	5
Pallet Quantity	1860

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL9460A](#)



A Hubbell brand