

# Straight Blade Devices, Male Plug, Nylon, 4-Position, Heavy Duty, Industrial/Commercial Grade, Angled, 3-Pole 4-Wire Grounding, 60A 125/250V, 14-60P.

By Hubbell Wiring Device-Kellems  
Catalog # [HBL9462C](#)



Straight Blade Devices, Male Plug, Nylon, 4-Position, Heavy Duty,  
Industrial/Commercial Grade, Angled, 3-Pole 4-Wire Grounding,  
60A 125/250V, 14-60P, Black, Single Pack.

## Features

- Nylon
- 4-Position
- Heavy Duty

## General

Catalog Number	HBL9462C
Color	Black
Cord Range	0.625"-1.310"
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	3
Material	Nylon
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Style	Grounding
Type	Plug
UPC	783585015361

## Dimensions

Dimensions	3.38 in x 4.5 in x 2.37 in
Height	2.37 in
Length	3.38 in
Weight	0.85 lb
Width	4.5 in

## Electrical Ratings

Amperage Rating	60 A
Current / Amperage Rating	60 A
Current Rating	60 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	<ul style="list-style-type: none"><li>• 125 V</li><li>• 250 V</li></ul>
Voltage Rating Description	125/250 V

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#12 AWG to #4 AWG

## Certifications And Compliance

Industry Standard(s)	UL Listed To UL 498 File E2186, Guide RTRT Fed Spec WC596G, Meets WD-6 Requirements, Certified To CSA, C22.2, No. 42 File 285
Nema Rating	14-60P

## Logistics

Carton Quantity	5
Pallet Quantity	765

## Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - HBL9462C](#)
- [Warranty - Industrial & Commercial Products](#)