

# Locking Devices, Twist-Lock®, Industrial, Male Plug, 20A 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL9965GCB](#)



Locking Devices, Twist-Lock®, Industrial, Male Insulgrip® Plug, 20A 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White nylon.

## Application

Extra Heavy Duty Industrial

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 - #8 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

## General

Catalog Number	HBL9965GCB
Color	Black, White
Cord Range	0.360"-0.930" (9-24)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Male Insulgrip® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> <li>• Assembly Screws - Steel - nickel plated</li> <li>• Blades - Brass</li> <li>• Housing / Cord Clamp - Nylon</li> <li>• Terminal Clamp - Cold rolled steel - nickel plated</li> <li>• Terminal Retainer - Clear polycarbonate</li> </ul>

- Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)

Type  
UPC

Plugs  
783585037622

## Dimensions

Dimensions	2.26 in x 2.26 in x 2.75 in
Display Size	Standard Sized
Height	2.75 in
Length	2.26 in
Weight	0.3 lb
Width	2.26 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V

## Conductor Related

Cable Range	0.360 - 0.930 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
Nema Rating	Non-NEMA
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	30
Pallet Quantity	3060

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL9965GCB](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL9965GCB-SPEC-EN | REV 10/2024