

Disconnect Switches, Non Fused, Hazardous Location, 100A 600V AC, 3-Pole with Aux Contact

By Hubbell Wiring Device-Kellems
Catalog # [HBLB7NFD21AA](#)



Disconnect Switches, Non Fused, Hazardous Location, 100A
600V AC, 3-Pole with Aux Contact

General

Catalog Number	HBLB7NFD21AA
Color	Gray
EU RoHS Indicator	No
Horsepower - Maximum	50
Item Type	Unfused Disconnect Switch with Auxiliary Contact
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	Disconnect Switch
Specifications	<ul style="list-style-type: none">• Conduit Sizes - 1½ NPT• Cover Bolts - Stainless Steel• Finish - Grey Powder Polyester painted exterior• O-Ring Gasket - Silicone• Terminal Wire Size - #8-1
Style	Unfused
Type	Switch with Aux Contact
UPC	783585242644

Dimensions

Dimensions	13.06 in x 8.13 in x 7.81 in
Height	7.81 in
Length	13.06 in
Width	8.13 in

Electrical Ratings

Amperage Rating	100 A
Current / Amperage Rating	100 A
Current Rating	100 A

Certifications And Compliance

Industry Standard(s)	UL98 Certified
----------------------	----------------

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Safety Product Guide](#)
[Specifications - HBLB7NFD21AA](#)
[Warranty - Industrial & Commercial Products](#)