

# Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, NEMA4XEnclosure,

By Hubbell Wiring Device-Kellems  
Catalog # [HBLDS3](#)



Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, Gray, NEMA4XEnclosure,

## Application

- Labelless

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage
- Electrical - Dielectric Voltage - Withstands 3000V AC minimum
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94-5VA and V0 Classification
- Environmental - Operating Temperature - Max Continuous 75°C, Min Continuous -40°C w/o impact
- Environmental - UV Resistance - All materials are UV stabilized
- Mechanical - Impact Resistance - In accordance with UL 746C
- Mechanical - Mounting - Non-Metallic - External fully adjustable feet
- Mechanical - Product Identification - Identification and ratings are part of external label
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

## General

Catalog Number	HBLDS3
EU RoHS Indicator	No
Horsepower - Maximum	15
Ingress Protection	IP69K
Mounting Method	External fully adjustable feet
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	<ul style="list-style-type: none"> <li>• Non-Fused</li> <li>• MotorQuick/LINKOSITY</li> </ul>
Specifications	<ul style="list-style-type: none"> <li>• Base - Valox®</li> <li>• Enclosure Gasket - Neoprene</li> <li>• Handle - Valox®</li> </ul>

Style	<ul style="list-style-type: none"> <li>• Shaft (Unfused) - Valox®</li> <li>• Top - Valox®</li> <li>• Heavy Duty</li> <li>• Replacement Switches</li> <li>• Disconnect Switches</li> <li>• Accessories For LINKOSITY®</li> </ul>
Type	
UPC	783585955001

## Dimensions

Dimensions	8.5 in x 6 in x 4.12 in
Height	4.12 in
Length	8.5 in
Weight	2.6 lb
Width	6 in

## Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 3000V AC minimum
Phase	Three Phase

## Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	1
Pallet Quantity	410

## Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - HBLDS3](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBLDS3-SPEC-EN | REV 10/2024