

# Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, NEMA 4X Enclosure, With 3) Aux Contacts

By Hubbell Wiring Device-Kellems  
Catalog # [HBLDS33ACNK](#)



Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, Gray, NEMA 4X Enclosure, With 3) Aux Contacts

## Application

- Labelless

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage
- Electrical - Dielectric Voltage - Withstands 3000V AC minimum
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94-5VA and V0 Classification
- Environmental - Operating Temperature - Max Continuous 75°C, Min Continuous -40°C w/o impact
- Environmental - UV Resistance - All materials are UV stabilized
- Mechanical - Impact Resistance - In accordance with UL 746C
- Mechanical - Mounting - Non-Metallic - External fully adjustable feet
- Mechanical - Product Identification - Identification and ratings are part of external label
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

## General

Catalog Number	HBLDS33ACNK
EU RoHS Indicator	No
Enclosure Type	Type 4X, IP69k
Mounting Method	External fully adjustable feet
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Non-Fused
Specifications	<ul style="list-style-type: none"><li>• Base - Valox®</li><li>• Enclosure Gasket - Neoprene</li></ul>

- Handle - Valox®
- Shaft (Unfused) - Valox®
- Top - Valox®

Style	Heavy Duty
Type	Disconnect Switches
UPC	783585392868

## Dimensions

Dimensions	8.5 in x 6 in x 4.12 in
Height	4.12 in
Length	8.5 in
Width	6 in

## Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 3000V AC minimum

## Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance	CM
Status	

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBLDS33ACNK](#)  
[Warranty - Industrial & Commercial Products](#)