

Industrial Grade, MotorQuick Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, With 1) Pre-Wired LINKOSITY Female Receptacle

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS3MQR](#)



Switches and Lighting Controls, Industrial Grade, MotorQuick Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Gray, With 1) Pre-Wired LINKOSITY Female Receptacle

Performance

- Electrical - Dielectric Voltage - 2,200V AC minimum for 1 minute
- Electrical - Electrical Life - 6,000 cycles with load
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94-5VA and V0 Classification
- Environmental - Operating Temperature - Max. continuous 75°C, Min. continuous -40°C
- Mechanical - Impact Resistance - UL746C
- Mechanical - Mechanical Life - 10,000 minimum cycles
- Mechanical - Terminal Accommodations - 30A, #14 AWG Min. - #10 AWG Max
- Mechanical - Terminal Torque - 30A, 20 inch pounds

General

Catalog Number	HBLDS3MQR
EU RoHS Indicator	No
Enclosure Type	Type 4X
Environmental Conditions	Indoor and Outdoor
Horsepower - Maximum	15
Ingress Protection	IP67
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	MotorQuick/LINKOSITY
Specifications	<ul style="list-style-type: none">• Contact Carrier - Nylon 6/6, white• Contact Materials - Brass pins• Contact Plating - Hard gold over palladium/nickel• Coupling Hardware - Nickel plated brass

Type
UPC

- Overmold Material - Glass filled polyurethane, gray
- Disconnect Switches
783585310930

Dimensions

Dimensions	8.5 in x 6 in x 4.12 in
Display Size	Standard Sized Product
Height	4.12 in
Length	8.5 in
Weight	2.95 lb
Width	6 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pre-Wired
Current Rating	30 A
Dielectric Strength	2,200V AC minimum for 1 minute
Phase	Three Phase
Wattage	18000

Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Listed to UL 2238 and UL 50E• UL 508, Industrial Control Equipment File #E36355
----------------------	--

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Safety Product Guide](#)
[Specifications - HBLDS3MQR](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand