



Wiring Device-Kellems

Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, Gray, No Knockouts

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS3NK](#)



Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, Gray, No Knockouts

Features

- Molded-in conduit opening and field installed hub
- Internal frame automatically bonds all grounds
- Reversible interior accommodates top or bottom conduit opening

Application

Labelless

General

Enclosure Type	Type 4X, IP69k
Mounting Method	External fully adjustable feet
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage • Electrical - Dielectric Voltage - Withstands 3000V AC minimum • Electrical - Max. Working Voltage - 600V AC RMS • Environmental - Flammability - UL94-5VA and V0 Classification • Environmental - Operating Temperature - Max Continuous 75°C, Min Continuous -40°C w/o impact • Environmental - UV Resistance - All materials are UV stabilized • Mechanical - Impact Resistance - In accordance with UL 746C • Mechanical - Mounting - Non-Metallic - External fully adjustable feet • Mechanical - Product
-------------	--

Dimensions

Dimensions	8.5 in x 6 in x 4.12 in
Height	4.12 in
Length	8.5 in
Width	6 in

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 3000V AC minimum

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Catalog Page - Wiring F-17 Catalog page](#)
- [Catalog Page - Wiring F-5 Catalog page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Warranty - Industrial & Commercial Products](#)

Identification -
Identification and ratings
are part of external label

- Mechanical - Terminal
Identification - In
accordance with UL, CSA
and international
conventions

Series

Non-Fused

Style

Heavy Duty

Type

- Disconnect Switches
- Disconnect Switches

UPC

783585841014



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBLDS3NK-SPEC-EN | REV 1/2024