

Disconnect Switches, Sloped Enclosure, 30A 600V AC, Non-Fused, NEMA 4X, Stainless Steel, With Aux Contact

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS3SSRAC](#)



Disconnect Switches, Sloped Enclosure, 30A 600V AC, Non-Fused, NEMA 4X, Stainless Steel, With Aux Contact

Features

- Formed in nonporous 304 stainless steel
- IP69k and Type 4X,12K water ingress protection
- Certified by NSF for hygiene in food processing applications
- Highly visible red handle which meets OSHA Lockout/Tagout capabilities
- Accepts up to 2 Auxiliary contacts

Application

Labelless

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage
- Electrical - Dielectric Voltage - Withstands 3000V AC minimum
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94-5VA and V0 Classification
- Environmental - Operating Temperature - Max Continuous 75°C, Min Continuous -40°C w/o impact
- Environmental - UV Resistance - All materials are UV stabilized
- Mechanical - Impact Resistance - In accordance with UL 746C
- Mechanical - Mounting - Stainless Steel - Feet are fixed
- Mechanical - Product Identification - Identification and ratings are part of external label
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

General

Catalog Number	HBLDS3SSRAC
EU RoHS Indicator	Contact Manufacturer
Enclosure Type	Type 4X, IP69k
Mounting Method	Feet are fixed

Operating Temperature

Maximum continuous 75°C and minimum -40°C without Impact Non-Fused

Series Specifications

- Base - #14 Gauge Type 304 Stainless Steel
- Enclosure Gasket - Neoprene
- Handle - Valox®
- Shaft (Unfused) - Valox®
- Top - #14 Gauge Type 304 Stainless Steel

Style Type UPC

Heavy Duty
Disconnect Switches
783585541556

Dimensions

Dimensions	8.6 in x 5.41 in x 4.92 in
Height	4.92 in
Length	8.6 in
Width	5.41 in

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 3000V AC minimum

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - HBLDS3SSRAC](#)
- [Warranty - Industrial & Commercial Products](#)