

Hose Reels, Low Pressure, .50" Diameter, 50 ' Length, Orange

By Hubbell Wiring Device-Kellems
Catalog # [HBLHR5050](#)



Hose Reels, Low Pressure, .50" Diameter, 50 ' Length, Orange

Application

Bench, Ceiling and Wall Mounted

General

Cable Length	50 Ft
Catalog Number	HBLHR5050
Construction	Steel
Duty	Heavy Duty
EU RoHS Indicator	No
Item Type	Low Pressure- 1/2" ID
Series	Air/Water/Liquid Industrial
Specifications	<ul style="list-style-type: none">• Cable Feet (m) - 50 (15.2)• Input Hose Fitting - 3/8• Max Pressure - 300• O.D. Inch (mm) - 0.77 (19.6)• Weight Lbs. (kg) - 44 (20.0)
Style	Input NPTF 3/8"

Type	Low Pressure 1/2" Id
UPC	783585243672

Dimensions

Cable Length Active	600
Reel Frame Dimension	Steel

Conductor Related

Nema Color	Orange
------------	--------

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBLHR5050](#)
[Warranty - Industrial & Commercial Products](#)