

Hose Reels, Low Pressure, .50" Diameter, 50 ' Length, Orange

By Hubbell Wiring Device-Kellems
Catalog # [HBLHR5050](#)



Hose Reels, Low Pressure, .50" Diameter, 50 ' Length, Orange

Application

Bench, Ceiling and Wall Mounted

General

| | |
|-------------------|--|
| Cable Length | 50 Ft |
| Catalog Number | HBLHR5050 |
| Construction | Steel |
| Duty | Heavy Duty |
| EU RoHS Indicator | No |
| Item Type | Low Pressure- 1/2" ID |
| Series | Air/Water/Liquid Industrial |
| Specifications | <ul style="list-style-type: none">• Cable Feet (m) - 50 (15.2)• Input Hose Fitting - 3/8• Max Pressure - 300• O.D. Inch (mm) - 0.77 (19.6)• Weight Lbs. (kg) - 44 (20.0) |
| Style | Input NPTF 3/8" |

| | |
|------|----------------------|
| Type | Low Pressure 1/2" Id |
| UPC | 783585243672 |

Dimensions

| | |
|----------------------|-------|
| Cable Length Active | 600 |
| Reel Frame Dimension | Steel |

Conductor Related

| | |
|------------|--------|
| Nema Color | Orange |
|------------|--------|

Logistics

| | |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBLHR5050](#)
[Warranty - Industrial & Commercial Products](#)