

# Heavy Duty Products, Single Pole Devices, Industrial Grade, Male-Female-Female-Female, Tri-Tap, 300/400A 600V AC/DC, Single Conductor, Pre-Wired

By Hubbell Wiring Device-Kellems  
Catalog # [HBLM3FBK](#)

Heavy Duty Single Pole Industrial Grade Male-Female-Female-Female, Tri-Tap, 300/400A 600V AC/DC, Single Conductor, Pre-Wired

## Features

- Industrial Grade
- Male-Female-Female-Female
- Tri-Tap

## Application

High Ampacity

## Performance

- Electrical - Amperage Rating - 400A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Mechanical - Product Identification - Ratings are a permanent part of the device

## General

Catalog Number	HBLM3FBK
Color	Black
EU RoHS Indicator	Contact Manufacturer
Insulation	Insulated Body
Item Type	Tri-Taps
Material	Brass and Elastomer
Number Of Pins	1) In, 3) Out- Male-Female-Female-Female
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Series 16



## Specifications

### Style

Type  
UPC

## Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Current Rating	400 A
Voltage Rating Description	600V AC/DC
Wattage	360000

## Certifications And Compliance

Industry Standard(s)	UL 498 And UL1691
----------------------	-------------------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Single Pole Devices](#)
- [Specifications - HBLM3FBK](#)
- [Warranty - Industrial & Commercial Products](#)